

DROP-IN

WiseCan



WiseCan I

Desiccant Capsule



Stable
hygroscopicity



The shell is
leak-proof



Material
Safety




Strong
and crack-resistant

WiseCan Desiccant Capsule is able to be placed underneath a product's lid or within the product packaging itself. It can rapidly absorb moisture thanks to its roll edge design. Overall, it is a great alternative to traditional desiccant bags. It has crack resistant shell and compact design, and is a great product for any pharmaceutical, OTC or diagnostic reagent product needing protection from the effects of humidity.

SPECIFICATION:

Spec	Product Code	W*L (mm \in)	Packaging Quantity
0.5g	60S-0.5A-PL I IEU	Φ13.8*10.5\Φ0.54*0.41	12000\ctn
1g	60S-1A-PL I IEU	Φ18.1*11.0\Φ0.71*0.43	8000\ctn
2g	60S-2A-PL I IEU	Φ24.8*11.0\Φ0.98*0.43	4500\ctn
3g	60S-3A-PL I IEU	Φ30.6*10.5\Φ1.20*0.41	3000\ctn
30g	60S-30A-PL I IEU	Φ63.0*18.5\Φ2.48*0.73	450\ctn



• Orange silica gel

STANDARD:

Item	Standard
Loss on Drying (302°F/150°C)	≤3.0%
Moisture absorption capacity (77°F/25°C)	RH = 20% ≥8.0%
	RH = 50% ≥20.0%



WiseSorbent Technology LLC

11 E Stow Rd, Marlton, NJ 08053, USA

wisesorbent.com

140 Rue du Canal du Midi - ZAC de La Masquere, 31750 Escalquens - France

wisesorbent.fr

No. 8 Lorong Jalak, Kawasan Perusahaan Kebun Baru, Batu 9, 42500 Telok Panglima Garang, Selangor, Malaysia

info@wisesorbent.com

