

DROP-IN

WiseMop



WiseMop

Liquids Absorber



Strong water absorption



Water soluble packaging



Absorb water quickly



Become solid after absorption

Used in hospitals, laboratories, nursing/elder care and other scenarios to quickly absorb/fix leaking liquids and prevent liquid contamination. It can absorb liquids within 1 min. After absorption, gel formation is easily to be collected and discard.

SPECIFICATION:

Spec	Product Code	W*L (mm\in)	Packaging Quantity
1g	2SP-1A-SR1EU	25*42\0.98*1.65	10000\ctn
2g	2SP-2A-SR1EU	25*52\0.98*2.05	6000\ctn
3g	2SP-3A-SR1EU	35*55\1.38*2.17	5000\ctn
5g	2SP-5A-SR1EU	35*65\1.38*2.56	3000\ctn



• Strong water absorption

Can absorb up to 350 times its own weight of distilled water, more than 40 times its own weight of normal saline.

STANDARD:

Item	Standard
Loss on Drying (221°F/105°C)	≤5.0%
Water absorption capacity	350-450g/g
Absorption capacity for 0.9% NaCl solution	40-45g/g
Absorption speed for the entire sachet	≤35s



WiseSorbent Technology LLC

11 E Stow Rd, Marlton, NJ 08053, USA

wisesorbent.com

140 Rue du Canal du Midi - ZAC de La Masquere, 31750 Escalquens - France

wisesorbent.fr

No. 8 Lorong Jalak, Kawasan Perusahaan Kebun Baru, Batu 9, 42500 Telok Panglima Garang, Selangor, Malaysia

info@wisesorbent.com

